

SUCTION VALVES FROM ENGINEERED SILICONE PRODUCTS



Designed for easy installation into all socket materials, ESP's suction valves are low profile, lightweight and durable. Reliable function provides the user with a secure suction suspension of the prosthetic socket while easy disassembly and cleaning insures optimal valve performance and longevity.

Lyn Valve RV

Designed for transfemoral applications, the Lyn Valve RV offers guaranteed reliability with no holes in valve body to clog or trap skin. Releases air at .5 psi without adjustment.

PA0002	Auto
PA0300	Manual



Lyn Valve BK

Designed for transtibial suction sockets, the Lyn Valve BK and BK2 (push button release) are auto expulsion valves that release air at .5 psi without adjustment. 7/8" diameter.

PA0200	BK
PA0202	BK2
PA0200M	BK Metric
PA0202M	BK2 Metric



Pee Wee Valve

Installed at the time of fabrication and molded directly into the thermo-plastic socket, the original Pee Wee Valve offers a low profile design for upper limb sockets.

PA0001



Pee Wee SI

A manually operated valve with high airflow capacity, the Pee Wee SI offers the same functionality as the original but may be retro-fit into a prefabricated socket. 9/16" diameter.

PA-PWSI



SUCTION VALVES — Continued

Part No.	Part/Accessory	Description
PA0120	Lyn Valve RV Insert Only	<i>Auto Expulsion</i>
PA0301	Lyn Valve RV Insert Only	<i>Manual Expulsion</i>
PA0002/D	Lyn Valve RV Molding Dummy Kit	
PA0002/T	Lyn Valve RV Disassembly Tool	<i>Used for disassembly of Lyn Valve RV Auto and Manual Expulsion valves.</i>
PA0002/P	Lyn Valve RV Plug Kit	<i>Allows for easy pull-in for transfemoral amputees.</i>
PA0014/RV	Lyn Valve RV Housing O-Ring	
PA0002/H	Lyn Valve RV Housing	
PA0002/N	Lyn Valve RV Aluminum Housing Nut	
PA0002/S	Lyn Valve RV Spring	
PA0002/W	Lyn Valve RV Wrench	<i>Used to loosen/remove Lyn Valve RV Insert and/or Aluminum Housing Nut.</i>
PA0080	Lyn Valve HV Plug Kit	<i>Designed for use with high vacuum socket systems. Reliable use to 25" of mercury. Allows for pull-in.</i>
PA0080/D	Lyn Valve HV Molding Dummy Kit	
PA0014/HV	Lyn Valve HV Seal O-Ring Set	
PA-LVD	Lyn Valve Diaphragm	<i>For Lyn Valve RV and Lyn Valve BK/BK2</i>
PA0222	Lyn Valve BK/BK2 Threaded Housing	<i>For installation of Lyn Valve BK/BK2 valves into soft thermoplastics.</i>
PA0222M	Lyn Valve BK/BK2 Metric Threaded Hsg.	<i>For installation of Lyn Valve BK/BK2 Metric valves into soft thermoplastics.</i>
PA0200/S	Lyn Valve BK/BK2 Spring	
PA0050	Flex Connect Kit	<i>For use with Lyn Valve RV. Creates a locking connection between flexible socket and support frame. Eliminates the need for Velcro® and rivets.</i>
PA0050/D	Flex Connect Molding Dummy Kit	
PA0050/N	Flex Connect Aluminum Nut	
PA-PWSI-T	Pee Wee Valve SI Tool	<i>Used for disassembly of Lyn Valve BK/BK2 and Pee Wee SI valves and reassembly of Pee Wee SI valve.</i>
PA-PWSI-H	Pee Wee Valve SI Threaded Housing	<i>For installation of Pee Wee SI valve into soft thermoplastics.</i>