

# VOLUME MANAGEMENT SOLUTIONS



## SHORTY SOFT-SOCK®

Shorty Soft-Sock is designed for use with elevated vacuum and total surface bearing sockets (TSB). They are short lengths to reduce volume mainly in the distal one third of the socket and remain below the suction sleeve. Color keyed for ease of patient instruction. Distal hole. Knit with easy care polyester. Sold each.

	TOP STRIPE	TOP	TOE	LENGTH
<b>1SPS-S1-81</b>	Red	4-3/4"	2-3/4"	7"
<b>1SPS-S1-91</b>	Red	5-3/4"	3-1/8"	5-5/8"
<b>1SPS-S1-82</b>	Black	3-1/8"	2-5/8"	3-5/8"
<b>1SPS-S1-92</b>	Black	4-1/2"	4"	3-1/4"



## PROXIMAL SOFT-SOCK®

For managing proximal volume changes. Tapered and open-ended Soft-Sock. Knit with polyester/Lycra®. Sold each.

			FITS		
LIGHTWEIGHT 3-PLY	5-PLY	SIZE	SOCK SIZES	LENGTH	
1PS1-RG-SH	1PS3-RG-SH	1PS5-RG-SH	Regular Short	1, 2	10.50" (27cm)
1PS1-RG-MD	1PS3-RG-MD	1PS5-RG-MD	Regular Medium	1, 2	14" (35cm)
1PS1-WD-MD	1PS3-WD-MD	1PS5-WD-MD	Wide Medium	3+	14" (35cm)
1PS1-XW-MD	1PS3-XW-MD	1PS5-XW-MD	X-Wide Medium	4+	14" (35cm)