

# ULTRA SEAL GEL LINER

A step above.

USHGL | USHGC | USLGL | USLGC



## DESCRIPTION

Introducing the revolutionary UltraSeal gel liner—a groundbreaking product that **seamlessly integrates advanced seal-in technology with the superior benefits of gel.**

With an integrated band available in two different heights, users will experience an airtight seal upon socket entry. When combined with OptiGel, this liner offers exceptional comfort and excellent conformity to the residual limb, ensuring a secure and snug fit that enhances control, comfort, and safety.

PART #	SUSPENSION	L-CODE
USHGL/USLGL	LOCKING	L5673
USHGC/USLGC	CUSHION	L5679

Recommended for all activity levels.



## WHY ULTRA GEL?

1

**It's the only seal-in liner available in gel.**

OptiGel has a smooth, soft texture that ensures gentle skin contact and a tailored fit around the residual limb.

INCREASED COMFORT

2

**It's made with less constrictive fabric.**

Outer knitted fabric combines strength, durability, and differentiated stretch for comfortable elasticity.

+ EASY TO DON & DOFF

3


**It's available in both locking and cushion.**

The locking feature ensures users are provided with a suspension that is secure, firm, and comfortable.

DUAL SUSPENSION


# CROSS SECTION DIAGRAM

1 THICKNESS | 2 RING HEIGHT OPTIONS | CUSHION & LOCKING



## HOW TO SIZE

Measurements taken 6cm from the distal end



## SIZING CHARTS

HIGH rings begin 7 inches from the center of the distal end.

LOW rings begin 5 inches from the center of the distal end.

MEASURED SIZE (CM)	HIGH RING LOCKING 3MM UNIFORM	HIGH RING CUSHION 3MM UNIFORM
20-21 cm	USHGL20	USHGC20
24-25 cm	USHGL24	USHGC24
26-27 cm	USHGL26	USHGC26
28-29 cm	USHGL28	USHGC28
32-34 cm	USHGL32	USHGC32
35-37 cm	USHGL35	USHGC35
38-40 cm	USHGL38	USHGC38
44-47 cm	USHGL44	USHGC44

MEASURED SIZE (CM)	LOW RING LOCKING 3MM UNIFORM	LOW RING CUSHION 3MM UNIFORM
20-21 cm	USLGL20	USLGC20
24-25 cm	USLGL24	USLGC24
26-27 cm	USLGL26	USLGC26
28-29 cm	USLGL28	USLGC28
32-34 cm	USLGL32	USLGC32
35-37 cm	USLGL35	USLGC35
38-40 cm	USLGL38	USLGC38
44-47 cm	USLGL44	USLGC44



T: 727.528.8566 | 800.574.5426 | F: 727.528.8862  
[www.easyliner.com](http://www.easyliner.com) | [info@easyliner.com](mailto:info@easyliner.com)  
 2895 42nd Avenue North St. Petersburg, Florida 33714

