

# ULTRA SEAL SILICONE LINER

A step above.

USHSL | USHSC | USLSL | USLSC



## DESCRIPTION

Experience the innovative UltraSeal silicone liner, carefully crafted to meet the needs of both transtibial and transfemoral amputees at all activity levels.

With an integrated band available at two different heights, users will enjoy an airtight seal upon socket entry. Combined with OptiSil, it provides exceptional comfort and optimized suspension for maximum convenience in daily use.

Additionally, the UltraSeal offers a dual suspension system that seamlessly harnesses the advantages of both locking suspension and Seal-In technology, delivering unmatched functionality.

| PART #      | SUSPENSION | L-CODE |
|-------------|------------|--------|
| USHSL/USLSL | LOCKING    | L5673  |
| USHSC/USLSC | CUSHION    | L5679  |

Recommended for all activity levels.



## WHY ULTRA?

1

### LESS CONSTRICTIVE.

Outer knitted fabric combines strength, durability, and differentiated stretch for comfortable elasticity.

+ EASY TO DON & DOFF

2

### LOCKING SECURITY.

The locking feature ensures users are provided with a suspension that is secure, firm, and comfortable.

DUAL SUSPENSION

3


### FRIENDLY SILICONE SURFACE.

OptiSil offers a thin, lightweight, and smooth inner surface with 1/5 the friction of regular silicone, ensuring superior skin conformance.

SKIN-FRIENDLY

# CROSS SECTION DIAGRAM

1 THICKNESS | 2 RING HEIGHT OPTIONS | CUSHION & LOCKING




LOW ring begins 5 inches from the center of the distal end.

HIGH ring begins 7 inches from the center of the distal end.

## HOW TO SIZE

Measurements taken 6cm from the distal end



## SIZING CHARTS

HIGH rings begin 7 inches from the center of the distal end.

LOW rings begin 5 inches from the center of the distal end.

| MEASURED SIZE (CM) | HIGH RING LOCKING<br>3MM UNIFORM | HIGH RING CUSHION<br>3MM UNIFORM |
|--------------------|----------------------------------|----------------------------------|
| 20-21 cm           | USHSL20                          | USHSC20                          |
| 22-23 cm           | USHSL22                          | USHSC22                          |
| 24-25 cm           | USHSL24                          | USHSC24                          |
| 26-27 cm           | USHSL26                          | USHSC26                          |
| 28-29 cm           | USHSL28                          | USHSC28                          |
| 30-31 cm           | USHSL30                          | USHSC30                          |
| 32-34 cm           | USHSL32                          | USHSC32                          |
| 35-37 cm           | USHSL35                          | USHSC35                          |
| 38-40 cm           | USHSL38                          | USHSC38                          |
| 41-43 cm           | USHSL41                          | USHSC41                          |
| 44-47 cm           | USHSL44                          | USHSC44                          |

| MEASURED SIZE (CM) | LOW RING LOCKING<br>3MM UNIFORM | LOW RING CUSHION<br>3MM UNIFORM |
|--------------------|---------------------------------|---------------------------------|
| 20-21 cm           | USLSL20                         | USLSC20                         |
| 22-23 cm           | USLSL22                         | USLSC22                         |
| 24-25 cm           | USLSL24                         | USLSC24                         |
| 26-27 cm           | USLSL26                         | USLSC26                         |
| 28-29 cm           | USLSL28                         | USLSC28                         |
| 30-31 cm           | USLSL30                         | USLSC30                         |
| 32-34 cm           | USLSL32                         | USLSC32                         |
| 35-37 cm           | USLSL35                         | USLSC35                         |
| 38-40 cm           | USLSL38                         | USLSC38                         |
| 41-43 cm           | USLSL41                         | USLSC41                         |
| 44-47 cm           | USLSL44                         | USLSC44                         |



T: 727.528.8566 | 800.574.5426 | F: 727.528.8862  
[www.easyliner.com](http://www.easyliner.com) | [info@easyliner.com](mailto:info@easyliner.com)  
 2895 42nd Avenue North St. Petersburg, Florida 33714

